

» Soft-Sock® Prosthetic Sock

Socks

Supplier:

Knit-Rite, Inc.

Features & Benefits:

- Wicks perspiration away from the skin and inhibits odor-causing bacteria
- Soft and cuddly feel
- Lycra® fabric provides stretch and fit qualities
- Insulates residual limb against the cold

Specifications:

- Styles: *Standard, with or without Hole-In-Toe*
- Materials: *Coolmax® or X-Static® blends*
- Thicknesses: *1 ply, 3 ply, 5 ply or 6 ply (see chart)*
- Sizes: *14 (see chart)**
(Not all sizes are available for the Hole-in-Toe or X-Static® models)*
- Lengths: *14 (see chart)**
(Not all lengths are available for the Hole-in-Toe or X-Static® models)*
- Wash fleece side in. Do not use bleach or fabric softener. Tumble dry, cool temperature

Indications:

- Protection and comfort of residual limb

Call Points:

- Prosthetist
- Prosthetic technician

Warranty:

- Against manufacturers defects



Soft-Sock® Prosthetic Sock » Knit-Rite, Inc.

Item No.	Item No.	Item No	Item No	Size	Fits Size	Length
1 Ply	3 Ply	5 Ply	6 Ply			
<i>With Coolmax®/Lycra® Fabrics</i>						
KR-1S-P1CH-XS	—	—	—	Child X-Short	A	15cm (6")
KR-1S-P1CH-SH	KR-1S-P3CH-SH	KR-1S-P5CH-SH	KR-1S-P6CH-SH	Child Short	A	20cm (8")
KR-1S-P1CH-12	KR-1S-P3CH-12	KR-1S-P5CH-12	—	Child Medium	A	30cm (12")
KR-1S-P1NA-SH	KR-1S-P3NA-SH	KR-1S-P5NA-SH	KR-1S-P6NA-SH	Narrow Short	B, 0, 1	25–35 cm (10–14")
KR-1S-P1NA-MD	KR-1S-P3NA-MD	KR-1S-P5NA-MD	KR-1S-P6NA-MD	Narrow Medium	B, 0, 1	40–50 cm (16–20")
KR-1S-P1NA-LG	KR-1S-P3NA-LG	KR-1S-P5NA-LG	KR-1S-P6NA-LG	Narrow Long	B, 0, 1	55–70 cm (22–28")
KR-1S-P1RG-XS	KR-1S-P3RG-XS	KR-1S-P5RG-XS	KR-1S-P6RG-XS	Regular X-Short	1, 2	20–30 cm (8–12")
KR-1S-P1RG-SH	KR-1S-P3RG-SH	KR-1S-P5RG-SH	KR-1S-P6RG-SH	Regular Short	1, 2	25–35 cm (10–14")
KR-1S-P1RG-MD	KR-1S-P3RG-MD	KR-1S-P5RG-MD	KR-1S-P6RG-MD	Regular Medium	1, 2	40–50 cm (16–20")
KR-1S-P1RG-LG	KR-1S-P3RG-LG	KR-1S-P5RG-LG	KR-1S-P6RG-LG	Regular Long	1, 2	55–70 cm (22–28")
KR-1S-P1WD-SH	KR-1S-P3WD-SH	KR-1S-P5WD-SH	KR-1S-P6WD-SH	Wide Short	3+	25–35 cm (10–14")
KR-1S-P1WD-MD	KR-1S-P3WD-MD	KR-1S-P5WD-MD	KR-1S-P6WD-MD	Wide Medium	3+	40–50 cm (16–20")
KR-1S-P1XW-SH	KR-1S-P3XW-SH	KR-1S-P5XW-SH	—	X-Wide Short	4+	25–35 cm (10–14")
KR-1S-P1XW-MD	KR-1S-P3XW-MD	KR-1S-P6XW-MD	—	X-Wide Medium	4+	40–50 cm (16–20")
<i>With Coolmax®/Lycra® Fabrics — Hole-In-Toe</i>						
KR-1S-PSCH-SH	KR-1S-P3SC-SH	KR-1S-P5SC-SH	KR-1S-P6SC-SH	Child Short	A	20cm (8")
KR-1S-PSNA-SH	KR-1S-P3SN-SH	KR-1S-P5SN-SH	KR-1S-P6SN-SH	Narrow Short	B, 0, 1	25–35 cm (10–14")
KR-1S-PSNA-MD	KR-1S-P3SN-MD	KR-1S-P5SN-MD	KR-1S-P6SN-MD	Narrow Medium	B, 0, 1	40–50 cm (16–20")
KR-1S-PSRG-XS	KR-1S-P3SR-XS	KR-1S-P5SR-XS	KR-1S-P6SR-XS	Regular X-Short	1, 2	20–30 cm (8–12")
KR-1S-PSRG-SH	KR-1S-P3SR-SH	KR-1S-P5SR-SH	KR-1S-P6SR-SH	Regular Short	1, 2	25–35 cm (10–14")
KR-1S-PSRG-MD	KR-1S-P3SR-MD	KR-1S-P5SR-MD	KR-1S-P6SR-MD	Regular Medium	1, 2	40–50 cm (16–20")
KR-1S-PSRG-LG	KR-1S-P3SR-LG	KR-1S-P5SR-LG	KR-1S-P6SR-LG	Regular Long	1, 2	55–70 cm (22–28")
KR-1S-PSWD-SH	KR-1S-P3SW-SH	KR-1S-P5SW-SH	KR-1S-P6SW-SH	Wide Short	3+	25–35 cm (10–14")
KR-1S-PSWD-MD	KR-1S-P3SW-MD	KR-1S-P5SW-MD	KR-1S-P6SW-MD	Wide Medium	3+	40–50 cm (16–20")
<i>With Polyester/Lycra®/X-Static® Fabrics</i>						
KR-1S-X1NA-SH	KR-1S-X3NA-SH	KR-1S-X5NA-SH	—	Narrow Short	B, 0, 1	25–35 cm (10–14")
KR-1S-X1RG-SH	KR-1S-X3RG-SH	KR-1S-X5RG-SH	—	Regular Short	1, 2	25–35 cm (10–14")
KR-1S-X1RG-MD	KR-1S-X3RG-MD	KR-1S-X5RG-MD	—	Regular Medium	1, 2	40–50 cm (16–20")
KR-1S-X1WD-MD	KR-1S-X3WD-MD	KR-1S-X5WD-MD	—	Wide Medium	3+	40–50 cm (16–20")