

» X-Wool® Prosthetic Sock

Socks

Supplier:

Knit-Rite, Inc.

Features & Benefits:

- Features X-Static® high performance fabric
- Absorbent and wicking to keep limb dry
- Antimicrobial properties inhibit growth of bacteria and fungi
- Keeps the residual limb cooler in summer and warmer in winter
- Thick and cushioning virgin wool
- Fleeced for softness and comfort
- Contours residual limb without stretching out
- Accommodates flexion
- Color coded to easily identify thickness

Specifications:

- Styles: *Standard, with or without Hole-In-Toe**
(* Hole-In-Toe available for certain 3 and 5 ply sizes only)
- Materials: *Wool and X-Static®/Lycra® blend*
- Thicknesses: *Three (see chart)*
 - 3 ply = *Yellow*
 - 5 ply = *Green*
 - 6 ply = *Gray*
- Sizes: *Four (see chart)*
- Lengths: *Six (see chart)*
- Machine washable

Indications:

- Protection and comfort of residual limb

Call Points:

- Prosthetist
- Prosthetic technician

Warranty:

- Against manufacturers defects



X-Wool® Prosthetic Sock » Knit-Rite, Inc.

Item No.	Item No	Item No	Size	Fits Size	Length
3 Ply	5 Ply	6 Ply			
Standard					
KR-1W-X3NA-XS	KR-1W-X5NA-XS	—	Narrow X-Short	00, 0, AS, AL	20–25 cm (8–10")
KR-1W-X3NA-SH	KR-1W-X5NA-SH	KR-1W-X6NA-SH	Narrow Short	00, 0, AS, AL	25–30 cm (10–12")
KR-1W-X3NA-RG	KR-1W-X5NA-RG	KR-1W-X6NA-RG	Narrow Regular	00, 0, AS, AL	35–40 cm (14–16")
KR-1W-X3NA-LG	KR-1W-X5NA-LG	KR-1W-X6NA-LG	Narrow Long	00, 0, AS, AL	45–50 cm (18–20")
KR-1W-X3MD-XS	KR-1W-X5MD-XS	—	Medium X-Short	1, 2	20–25 cm (8–10")
KR-1W-X3MD-SH	KR-1W-X5MD-SH	KR-1W-X6MD-SH	Medium Short	1, 2	25–30 cm (10–12")
KR-1W-X3MD-RG	KR-1W-X5MD-RG	KR-1W-X6MD-RG	Medium Regular	1, 2	35–40 cm (14–16")
KR-1W-X3MD-LG	KR-1W-X5MD-LG	KR-1W-X6MD-LG	Medium Long	1, 2	45–50 cm (18–20")
KR-1W-X3MD-XL	KR-1W-X5MD-XL	—	Medium X-Long	1, 2	55–60 cm (22–24")
KR-1W-X3MD-XX	KR-1W-X5MD-XX	—	Medium XX-Long	1, 2	65–70 cm (26–28")
KR-1W-X3WD-SH	KR-1W-X5WD-SH	KR-1W-X6WD-SH	Wide Short	3, 4	20–25 cm (8–10")
KR-1W-X3WD-MD	KR-1W-X5WD-MD	KR-1W-X6WD-MD	Wide Medium	3, 4	25–30 cm (10–12")
KR-1W-X3WD-LG	KR-1W-X5WD-LG	KR-1W-X6WD-LG	Wide Long	3, 4	35–40 cm (14–16")
KR-1W-X3WD-XL	KR-1W-X5WD-XL	—	Wide X-Long	3, 4	45–50 cm (18–20")
KR-1W-X3WD-XX	KR-1W-X5WD-XX	—	Wide XX -Long	3, 4	55–60 cm (22–24")
KR-1W-X3EW-SH	KR-1W-X5EW-SH	—	X-Wide Short	5, 6	30–35 cm (12–14")
KR-1W-X3EW-MD	KR-1W-X5EW-MD	—	X-Wide Medium	5, 6	40–45 cm (16–18")
With Hole-In-Toe					
KR-1W-X3NA-XS	KR-1W-X5NA-XS	—	Narrow X-Short	00, 0, AS, AL	20–25 cm (8–10")
KR-1W-X3NA-SH	KR-1W-X5NA-SH	—	Narrow Short	00, 0, AS, AL	25–30 cm (10–12")
KR-1W-X3NA-RG	KR-1W-X5NA-RG	—	Narrow Regular	00, 0, AS, AL	35–40 cm (14–16")
KR-1W-X3NA-LG	KR-1W-X5NA-LG	—	Narrow Long	00, 0, AS, AL	45–50 cm (18–20")
KR-1W-X3MD-XS	KR-1W-X5MD-XS	—	Medium X-Short	1, 2	20–25 cm (8–10")
KR-1W-X3MD-SH	KR-1W-X5MD-SH	—	Medium Short	1, 2	25–30 cm (10–12")
KR-1W-X3MD-RG	KR-1W-X5MD-RG	—	Medium Regular	1, 2	35–40 cm (14–16")
KR-1W-X3MD-LG	KR-1W-X5MD-LG	—	Medium Long	1, 2	45–50 cm (18–20")
KR-1W-X3WD-SH	KR-1W-X5WD-SH	—	Wide Short	3, 4	20–25 cm (8–10")
KR-1W-X3WD-MD	KR-1W-X5WD-MD	—	Wide Medium	3, 4	25–30 cm (10–12")