

**PDQ Mini Mobile Oven**  
**Portable Oven**

**Vendor:**

OTS-Corp.

**Practitioner Benefits:**

- Heat low-temperature plastic without need of a hydrocollator; no need to dry product before use
- Easy to carry for outclinic intervention

**Features:**

- Rocker switch to turn on or off
- Digital Controller cycles heating plate on and off depending on the setpoint and the temperature in the oven
- Maintains the temperature within 2% of setpoint
- Controller can be programmed to indicate degrees in Fahrenheit or Centigrade
- For safety, oven temperature is preset to reach a maximum of 170° F (71° C)

**Specifications:**

- Dimension external: 29" x 31.5" x 5"
- Dimension internal: 26" x 26"
- Weight: 29.5 lbs.
- Electrical requirements: 120 v; 50/60 hz; 15 amp
- Temperature range: 0–170° F

**Indications:**

- Heating low-temperature plastics

**Contraindications:**

- Caution for temperatures exceeding 175° F
- Oven exterior shell not insulated for high temperature

**Call Points:**

- Orthotist
- Occupational therapist
- Orthotic technicians

**Warranty:**

- Six month manufacturer's warranty against material defects and workmanship under normal use and service
- Extended warranty available: covers silicone heating element for an additional period of 1 year and electronic controller for 2 years



**OTS-Corp., PDQ Mini Mobile Oven**

Item No.	Description
OTS-OMINIMOBILE	PDQ Mini Mobile Oven
OTS-ORWARRANTY-MINI	Extended Warranty
OTS-OBAG	Carry Bag—attaches to oven to hold 2 sheets low-temp. plastic (24" x 36") plus tools