

## » Icelock® Clutch 211

### Lock

#### Supplier:

Ossur Americas

#### Features & Benefits:

- Low build height and lightweight
- Easy release unlocking mechanism
- Delrin push button can be shortened
- Pin tunnel creates space for attachment pin
- Rotation control on lamination/thermoformable ring
- Wear-resistant stainless steel pin guide

#### Specifications:

- Types: *Clutch lock with or without adapter*  
(Titanium 272 and Stainless steel 273)
- Weight limit: *With titanium adapter 272= 166kg (365lbs)*  
*With stainless steel adapter 273= 100kg (220lbs)*
- Weight: 78g (2.8oz)
- Build height: 21mm ( $1\frac{3}{16}$ "
- Secure clutch mechanism tested to tolerate 300kg (660lbs) pull
- Delrin push button

#### Indications:

- All amputation levels
- Recommended for transfemoral amputees

#### Call Points:


- Prosthetist
- Prosthetic technician

#### Warranty:

- One year, against manufacturers defects




ICELOCK Clutch  
211



With Pyramid Adapter

ICELOCK Clutch  
211



Without Pyramid Adapter

**Icelock® Clutch 211 » Ossur Americas**

Item No.	Model	Description	Weight Limit	Build Height	Weight
OS-L-211000	211	Clutch lock <i>(without adapter)*</i>	—	21mm ( <sup>13</sup> / <sub>16</sub> "	78g (2.8oz)

**Adapters**

OS-L-272000	272	Titanium pyramid	166kg (365lbs)	9mm ( <sup>3</sup> / <sub>8</sub> "	76g (2.7oz)
OS-L-273000	273	Stainless steel pyramid	100kg (220lbs)	8mm ( <sup>5</sup> / <sub>16</sub> "	64g (2.3oz)

\* Includes OS-L-292000 attachment pin

**Parts**

Item No.	Description
<b>For Clutch</b>	
OS-L-292000	Attachment pin clutch with cap, 12 notches, 40mm (1½") length — standard
OS-L-292003	Attachment pin clutch with cap, 7 notches, 22mm ( <sup>7</sup> / <sub>8</sub> ") length — short
OS-L-292005	Attachment pin clutch with cap, 17 notches, 52mm (2") length — long
OS-L-292020	Clutch mechanism and T-wrench
OS-L-293060	T-wrench
OS-L-193100	Protector cap <i>(for pin)</i>
OS-L-292131	Aluminum release button
OS-L-292015	Lock body with guide <i>(without dummy screw)</i>
OS-L-292122	Dummy screw
OS-L-292126	Delrin guide
OS-L-293045	Silicone seal
OS-L-292121	Pin tunnel <i>(with O-ring)</i>
OS-L-293046	O-ring 10 x 1½ <i>(for pin tunnel)</i>
OS-L-693127	O-ring 8 x 2 <i>(for pyramid bolt)</i>
OS-L-292032	Long pyramid bolt <i>(with O-ring)</i>
<b>For Adapters</b>	
OS-L-292135	Titanium pyramid <i>(with spacer and O-ring)</i>
OS-L-292136	Stainless steel pyramid <i>(with O-ring)</i>
OS-L-293046	O-ring 10 x 1½ <i>(for pin tunnel)</i>
OS-L-692142	Pyramid cap
OS-L-292032	Pyramid bolt, long with O-ring <i>(for 272 pyramid)</i>
OS-L-692032	Pyramid bolt with O-ring <i>(for 273 pyramid)</i>
OS-L-293048	Silicone fill <i>(for 272 pyramid)</i>
OS-L-293049	Silicone fill <i>(for 273 pyramid)</i>
OS-L-693127	O-ring 8 x 2 <i>(for pyramid bolts)</i>